



NOTES:

1. THE ANSI Z358.1-2009 STANDARD SPECIFIES EYEWASH NOZZLE HEIGHTS TO BE 33 IN. TO 45 IN. ABOVE THE FLOOR AND 6 IN. MINIMUM FROM WALL OR NEAREST OBSTRUCTION.
2. INSTALL SO THAT EYEWASH HEAD IS OVER SINK WHEN ACTIVATED. EYEWASH REQUIRES 4-1/2" OF CLEARANCE AROUND HEAD FOR FACEWASH STREAMS.
3. DRILL ONE Ø7/8" HOLE AND ONE Ø3/32" HOLE WHERE UNIT IS TO BE INSTALLED. REFER TO MOUNTING HOLE DETAIL. GO TO P102C OR THE LATEST REVISION FOR SHOWER DETAIL REFERENCE.
4. THESE DIMENSIONS MAY VARY ±1/2".
5. ALL SUBSTITUTE MUST BE APPROVED BY LBNL PROJECT MANAGER & EH&S.
6. SEE P102C OR THE LATEST REVISION FOR SHOWER DETAIL AND ELECTRICAL REQUIREMENT.

SINGLE ACTION PULL DOWN MODEL 7610 EMERGENCY EYE/FACEWASH & SHOWER INSTALLATION DETAIL

X
XX

SCALE: NONE

LBNL STANDARD
EMERGENCY EYE/FACE WASH & SHOWER INSTALLATION DETAIL
SINGLE ACTION PULL DOWN MODEL 7610

| | | | |
|---------------|-----|-------|------------|
| DRAWN BY | RZT | DATE | 12/22/2011 |
| CHECKED BY | MCD | DATE | 12/22/2011 |
| APPROVED BY | MCD | DATE | 12/22/2011 |
| CAD FILE PATH | | | |
| SCALE NTS | | | |
| DRAWING NO. | | SHEET | |
| P 1 1 0 A | | | |
| PROJECT NO. | | | |

UNIVERSITY OF CALIFORNIA LAWRENCE BERKELEY NATIONAL LABORATORY
FACILITIES DIVISION